



ENGLISH

Datasheet

Stock No. 918-6421

RS Pro 4 piece TCT Holesaw Kit, 12mm Cutting Depth



Specifications:

Article No. 918-6421

Material: Tungsten Carbide Tip

Shank Dia.: 10mm

Cutting depth: 12mm

Set Contents: 22-29-35mm, 1pc pilot drill

Feature:

The non-uniform separation of cutting edges and the integral body construction design virtually prevent vibration and resonance;

Ejector spring, Ø6mm pilot drill and screw are fitted for all diameters.

Application:

Cuts stainless steel, mild steel, iron, copper & brass sheet up to 3mm

Size(mm)	Stainless steel(rpm)	Steel(rpm)
18~21	300-700	700-1000
22~30	200-450	500-800
31~40	175-315	300-600
41~50	125-225	200-500
51~60	95-195	200-400
61~76	80-150	150-300
above 80	60-120	100-200