



## AS SC SCS SCT TL44

E1441345

Assortment Box Splicing & Branch Connectors 510pcs, .



### Product Properties:

Type of locking/unlocking	Lever
Nominal voltage	450 V
Nominal current	32 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	2-5 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Colour	Green

### Dimensions:

Max. AWG-size	12
Min. AWG-size	Other
Nominal cross section (device side)	0.2-4 mm <sup>2</sup>
Nominal cross section (installation side)	0.2-4 mm <sup>2</sup>
Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-2.5 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.2-4 mm <sup>2</sup>
Width	415 mm
Height	61 mm
MOQ	1 .

Unit	pcs
Nominal cross section	0.2-4 mm <sup>2</sup>
Length	330 mm
Nominal voltage	450 V

### **Approvals:**

Approved according to CE	Yes
--------------------------	-----

### **Compliance:**

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

### **Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Product Group	Splicing Connectors - Assortment Boxes
Search Description	SORTIMENT TOPP, SKARV & AVGRENINGSKLÄMMOR, 510ST
Alternative SKU	ASSCSCSSCTTL44
E-no	E1441345

### **Logistic information:**

Barcode	733117641531
Country of origin	CN
E-no	E1441345
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	AS SC SCS SCT TL44
Taric code	85369010
Unit	pcs

\*We reserve the right to make technical changes and disclaim any typographical errors.