



ENGLISH

Datasheet

Stock No: 480-197

RS Pro 37 way IDC snap-together D hood



Product Details

IDC Superfast Hoods

Snap-together hood for high speed assembly

Designed for IDC metal shell D connectors (0.05in.) pitch and commercial ranges

4.40 UNC thread finder screws included

| Dimensions (mm) | | | | |
|----------------------|----|----|----|----|
| No. of ways | 9 | 15 | 25 | 37 |
| Width | 20 | 20 | 20 | 20 |
| Height (inc. screws) | 56 | 56 | 56 | 56 |
| Length | 39 | 48 | 61 | 78 |

Note

Connector & cable not included.

Specifications:

| | |
|--------------------|----------|
| Number of Contacts | 37 |
| Housing Material | PET |
| Body Orientation | Straight |