

Technical data sheet

Article number:
924-00441

QDF2-6F

Product Group	Quick Connect Fully Insulated Female Funnel Entry 105 °C
Product Family	Double Grip Pre-Insulated Terminals
Material	Brass (BS), Polyamide 6.6 (PA66), Copper (CU)
Colour	Blue (BU)
Application Range	Low Voltage
Conductor Size Range mm²	1.5-2.5 mm ²
Diameter (D)	5 mm
Halogen-free	Yes
Length (L)	22 mm
Length (L2)	11 mm
Max Current	15 A
Max Voltage	300 V
Operating Temperature	+105 °C
Package Content	100 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	9 mm
Width (W2)	6.7 mm

