



Part Number : 1301090007

Product Description : Safeway Nylon 100W Hand Lamp with Molded, 16/3 SJTOW Cord Type, Metal Guard, Overall Cord Length 7.62m (25.0')

Series Number : 130109

Status : Active

Product Category : Lamps and Lights

Engineering Number : 402



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130109
Description	Safeway Nylon 100W Hand Lamp with Molded, 16/3 SJTOW Cord Type, Metal Guard, Overall Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
Product Name	Safeway
Type	Hand Lamps
UPC	78678861601

Agency

UL	E59049
----	--------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SJTOW
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Steel
Height	N/A
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	1078.188/g
Outlet	None
Packaging Type	Carton

This document was generated on Mar 27, 2025