



D40Z-1C5-S

Safety non-contact door switch, Cat 4/Ple, 5m cable, switch only

Specifications

Switch without actuator	✓
Min. operating distance OFF to ON	5 mm
Max. operating distance ON to OFF	15 mm
Max. differential travel	20 %
Ambient temperature (operating)	-10-65 °C
Vibration resistance	10 to 55 to 10 Hz (single amplitude: 0.75 mm, double amplitude: 1.5 mm)
Min. shock resistance	300 m/s ²
Degree of protection (IP)	IP67
Material housing	PBT
Mounting method	M4 screws
Max. power consumption	0.5 W
Auxiliary monitoring output	Photocoupler output: 24 V DC, load current: 10 mA
Cable length	5 m
Number of connectable switches	30 max. (wiring length: 100 m max.)
LED indicator	✓

Accessories



D40Z-1C-A

Safety non-contact door switch, Cat 4/Ple, actuator only



D40Z Datasheet

EN PDF 2.42 MB



D40Z Instruction Instruction Manual

EN PDF 10.6 MB



D40Z Safety Door Switch Discontinuation Discontinuation Notice

EN PDF 1.01 MB



Machine Safety Catalogue

EN PDF 9.91 MB



Safety Component Selection Guide EU Brochure

EN PDF 5.26 MB



Safety Interlock Switches Brochure

EN PDF 1.52 MB



Safety Solution Advanced Guide Guide

EN PDF 2.57 MB



Safety Solution Basic Guide Guide

EN PDF 14.4 MB