Features

- For SF24 Square Flange Panel Connectors
- IP67 (when mated)
- SF24 Series
- Push-Pull Coupling
- Used in Factory Automation, Robotics, Industrial Machinery, Railway & Transportation, Aerospace & Defence, Medical Equipment, Renewable Energy Systems etc.

RS PRO Circular Connector Dust Caps

RS Stock No.: 868161



Image for representational purposes only

RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The RS Pro SF24 Series offers a range of high-precision, waterproof connectors designed to meet IP67 sealing standards. Featuring a push-pull coupling mechanism, these connectors ensure fast, secure, and reliable mating. The chrome-plated brass housings provide excellent durability while maintaining a sleek, professional appearance.

Available in in-line cable-to-cable and cable-to-panel configurations, the series includes plugs and receptacles with either male pins or female sockets. Suitable for both data and power transmission, the RS Pro SF24 Series is ideal for use in medical, communications, and test & measurement applications.

General Specifications

Shell Material	Brass with chrome plating
Mating Type	Push-Pull
Mating Cycles	500
Colour	Silver

Mechanical Specifications

Connector Series	SF24

Operation Environment Specifications


Operating Temperature	-40^{0}C to 85^{0}C

Protection Category

IP Rating	IP67 (when mated)

Approvals

Compliance/Certifications	RoHS, CE



Mating Parts

Square Flange Panel Connectors	868148 868149 868150 868151 868152 868153 868154 868155 868156 868157 868158 868137 868138 868139 868140 868141 868142 868143 868144 868145 868146 868147