

RJ45, CAT 5E, CAT 6, CAT 6A PATCH CORDS

RJ45/RJ45 Cat 5E 100 ohms over-moulded patch cords «GENERIC» and «CHANNEL»

Designation	Length	PVC Generic Reference	PVC Channel Reference
UTP CAT 5E patch cords Grey over-moulded patch cord	0,50 m	CR503NB0.5	SPE191015-05GS
	1 m	CR503NB1	SPE191015-10GS
	2 m	CR503NB2	SPE191015-20GS
	3 m	CR503NB3	SPE191015-30GS
	5 m	CR503NB5	SPE191015-50GS
Coiled in individual polybag	10 m	CR503NB10	SPE191015-100GS
	0,50 m	CR503B0.5	SPE191016-05GS
	1 m	CR503B1	SPE191016-10GS
	2 m	CR503B2	SPE191016-20GS
	3 m	CR503B3	SPE191016-30GS
FTP CAT 5E patch cords Grey over-moulded patch cord	5 m	CR503B5	SPE191016-50GS
	10 m	CR503B10	SPE191016-100GS
	0,50 m	CR503BB0.5	
	1 m	CR503BB1	
	2m	CR503BB2	
Coiled in individual polybag	3m	CR503BB3	
	5 m	CR503BB5	
	10 m	CR503BB10	

LSOH on request.



RJ45/RJ45 Cat 6 100 ohms over-moulded patch cords «GENERIC» and «CHANNEL»

Designation	Length	Reference LSOH Generic	Reference PVC Channel
UTP CAT 6 patch cords Grey over-moulded patch cord	0,50 m	CR603NB0.5	SPE191228-05GS
	1 m	CR603NB1	SPE191228-10GS
	2 m	CR603NB2	SPE191228-20GS
	3 m	CR603NB3	SPE191228-30GS
	5 m	CR603NB5	SPE191228-50GS
Coiled in individual polybag	10 m	CR603NB10	SPE191228-100GS
	0,50 m	CR603B0.5	SPE191224-05GS
	1 m	CR603B1	SPE191224-10GS
	2 m	CR603B2	SPE191224-20GS
	3 m	CR603B3	SPE191224-30GS
FTP CAT 6 patch cords Grey over-moulded patch cord	5 m	CR603B5	SPE191224-50GS
	10 m	CR603B10	SPE191224-100GS



CR503XX

All references available with crossed cabling scheme, for example : CRC503B1, according to requested length, for example : CR503B7 (7 m), coloured patch cords (coloured cable with neutral over moulding).

VT = green, BL = blue, JN = yellow, RG = red. –
Example : CR503B0.5VT (Generic)
Example : SPE191016-05VT (Channel)