

Datasheet

RS Pro Straight 50 Ω Cable Mount BNC Connector Plug, Crimp Termination

RS Stock No: **546-5036**



Product Details

RS Pro cable mount BNC connector plug has nickel plated body, gold plated centre contact and is suitable for RF coaxial cable types. This 50 Ω straight BNC connector plug comes with bayonet coupling and a cable crimp termination. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Nickel plated body
- Gold plated centre contact
- Crimp termination method

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Cable Type	RG58, BT 2003, T/Enet, Ch/Net, Scart, RG59, BT 2003, Mini RG59, RG174, RG178, PSF 1/2, PSF 1/3, RG179
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	4 GHz
Polarity	Normal
Termination Method	Crimp
Body Material	Brass
Insulation Material	PTFE
Operating Temperature Range	-20 to +80°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)