

TORX® T-Handles & Sets - ProGuard™ Finish

- Fits all TORX® and Star screws
- Solid steel handles
- Welded handle/blade connection
- Ergonomic handle design
- Flywheel effect saves time
- Smooth, non-porous handle coating



High Torque Steel


Up to 20% stronger, with more torque and twice the



Corrosion-resistant finish: Environmentally safe, provides better tool grip, resists solvents and is 5 times more corrosion

PART#	MODEL#	PCS	LENGTH	W/STAND	CONTENTS	QTY SETS
33034	TTHX8	8	Graduated	✓	T9, T10, T15, T20, T25, T27, T30, T40	1 TORX®

✓ Comes with stand



SIZE	INCH	MM	INCH	MM	PART#
T9	6.1	155	3.0	76	33009
T10	6.4	161	3.0	76	33010
T15	6.6	168	3.0	76	33015
T20	6.9	174	3.0	76	33020
T25	7.1	180	3.0	76	33025
T27	7.4	187	4.0	102	33027
T30	7.6	193	4.0	102	33030
T40	7.9	199	4.0	102	33040
T45	8.1	206	5.0	127	33045
T50	8.4	212	5.0	127	33050
T55	8.6	218	5.0	127	33055

Bondhus Corporation
1400 E Broadway • PO Box 660 • Monticello, MN 55362
Tel: 763-295-2162 • Toll Free: 800-328-8310 • Fax: 763-295-4440

Bondhus, Protanium, ProGuard, BriteGuard, GoldGuard and BallStar are trademarks of Bondhus Corporation.

TORX® and TORX PLUS® are registered trademarks of Acument Intellectual Properties, LLC.