

Label sheet, DIN A4 - BMKL 15X 9 YE CUS - 0824240

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Label sheet, DIN A4, can be ordered: Sheet, yellow, labeled according to customer specifications, Mounting type: Adhesive, Lettering field: 15 x 9 mm



The figure shows a version of the article

Why buy this product

- These labels have been specially developed for laser printers
- The unperforated SK U ... sheets are available for custom label designs
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 351157 |
| Weight per Piece (excluding packing) | 9.0 g |
| Custom tariff number | 39199000 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------|-------|
| Length (b) | 15 mm |
| Width (a) | 9 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

General

| | |
|-----------------------|---------------|
| Color | yellow |
| Base element material | Polyester |
| Components | Silicone-free |

Label sheet, DIN A4 - BMKL 15X 9 YE CUS - 0824240

Technical data

General

| | |
|-------------------------------------|-----------------------------|
| Material | Polyester |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 290 |
| Number of individual labels per row | 10 |
| Marking mounting type | Adhesive |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |