



TECHNICAL DATA SHEET

RS 764-3039 Matt Black Paint

A quick drying, high quality, universal spray paint based on alkyd resins. It exhibits excellent coverage and hardness characteristics and is ideally suited for use in manufacturing, repair and for home and workshop use.

- 100% Ozone Friendly
- Excellent coverage & flow
- Fast drying with high opacity
- Excellent hardness
- Very good resistance to water and other and chemicals
- Excellent adhesion to bare metal

Typical Properties

Drying time:	15 minutes (surface) 3 hours (touch dry) 24 hours (fully dry)
Maximum Temperature	110°C

Description

Matt Black Paint

Packaging

400 ml aerosol

Order Code

RS 764-3039

Directions for Use

- Ensure that surface is dry, smooth and free from dust and grease.
- To test, paint a sample panel in advance. Check synthetic and plastic substrates for adhesion and compatibility. For plastics such as PP and EPDM, a primer coat should be applied first.
- Shake the spray-can well for at least 2 minutes and at intervals during use.
- Spray, (holding the aerosol vertically), at a distance of 25-30 cm from the object to be painted. Best results are obtained by applying several thin coats rather than one single thick coat. Wait a few minutes, with a maximum of 30 minutes, between the applications of each layer.
- After use, clear the valve by spraying with the can inverted
- If repainting is necessary, this should be after 24 hours. Drying of the synthetic paint depends on the thickness of the layer and the ambient temperature.