

**ZMA35/70** **Precision locknut**

Precision locknuts ZMA, locking pegs, radially arranged, heavy series

Technical information**Main Dimensions & Performance Data**

d	M35X1,5	Thread
D	70 mm	Outside diameter
h	30 mm	Height
M _A	5 Nm	Mounting torque set screw
F _{aB}	460,000 N	Breaking load, axial
M _L	80 Nm	Breakawag
M _{AL}	40 Nm	Mounting torque reference
M _M	5.2 kg*cm ²	Mass moment of inertia
≈m	0.657 kg	Weight

Dimensions

d ₁	64 mm	Plant diameter outside
t	2.5 mm	Hight retaining slot
b	6 mm	Width retaining slot
c	15 mm	Distance bore
m	M6	Threaded - threaded pin