

TOREX TROUSERS

23MTR1901

- Multi-pocket trousers with 4-way stretch parts at crotch and sides for extra freedom of movement
- Slim fit
- Canvas stretch fabric with Coolmax[®] technology, moisture wicking and quick drying features
- Pre shaped knees
- 2 side pockets
- 1 ruler pocket with mobile pocket
- 1 thigh pocket with small pocket
- 2 back pockets
- 1 hammer loop
- Extendable hem
- EN ISO 13688:2013



Composition

- Main fabric: 47% cotton - 31% polyester - 22% T400 Lycra[®] Coolmax[®] 240g/m²
- 4-way stretch fabric: 93% polyamide - 7% elastane

Size

36 - 38 - 40 - 42 - 44 - 46 - 48 - 50 - 52 - 54 - 56

Color



Technologies



Multipocket

This item has 5 or more pockets for storing different articles and accessories.



4 way stretch fabric

Four-way (or 4-way) stretch means a fabric stretches and recovers both width and lengthwise



Small size 36

Size 36 is available for these trousers



Extra freedom of movement

This item has been especially developed to ensure an optimal freedom of movement.



3 stitches

A stitch is a single turn or loop of thread, or yarn.



Phone pouch

This item has a special compartment for carrying a cellular phone.



Extendable Hem

These pants have an extendable hem of 5cm that allows you to set your own ideal length and fit.

Fabrics

- Wasa
- YKK
- Coolmax®

Certificates



EN ISO 13688

General requirements for protective clothing.

[Read More](#)