

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1502070002](#)
Status: **Active**
Overview: [Ditto Wire-to-Wire Interconnects](#)
Description: Ditto Wire-to-Wire Interconnects, Single-Ended Pigtail Harness, 2.50mm Pitch, 0.30m Length, 3 Circuits

Documents:

Drawing (PDF)	Test Summary TS-36876-001-001 (PDF)
Product Specification PS-36876-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable Assemblies
Series	150207
Application	Power, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Ditto-to-Pigtail
Overmolded	No
Overview	Ditto Wire-to-Wire Interconnects
Product Name	Ditto
Type	Discrete Wire Assembly
UPC	889056240925

Physical

Cable Length	0.30m
Circuits (Loaded)	3
Color - Resin	White
Gender	Hermaphroditic
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	7.047/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Single Ended	Yes
Wire Size AWG	20, 22, 24, 26
Wire/Cable Type	UL 1061

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	350V AC

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	KAB2290L0.3V01
--------------------	----------------

Reference - Drawing Numbers

Product Specification	PS-36876-001-001
Sales Drawing	SD-150207-0001
Test Summary	TS-36876-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[150207](#) Series

Mates With

[36877](#) Ditto Hermaphroditic Crimp Housing

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION