

RJ45 DIN-rail outlet for keystone jacks



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 851 0000
Specification	RJ45 DIN-rail outlet for keystone jacks
HARTING eCatalogue	https://harting.com/09458510000

Identification

Category	Accessories
Series	HARTING RJ Industrial®
Type of accessory	Distribution module

Version

Size	Keystone version
Fixing	35 mm DIN rail acc. to EN 60715

Technical characteristics

Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-20 ... +70 °C
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

PROFINET	Yes
----------	-----

Commercial data

Packaging size	1
Net weight	4.892 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140064850
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400