



**Part Number :** [09508031](#)  
**Product Description :** KK 3.96mm Crimp  
Terminal Housing, Friction Ramp, 3 Circuits,  
Natural  
**Series Number :** 41695  
**Status :** Active  
**Product Category :** Connector Housings  
**Engineering Number :** 41695-N-B3



Documents & Resources

Drawings

[Drawing 009508031\\_sd.pdf](#)  
[Packaging Design Drawing PK-41695-001-001.pdf](#)

3D Models and Design Files


[3D Model 009508031\\_stp.zip](#)

Specifications

[Product Specification PS-08-50-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC

- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Connector Housings
Series	41695
Description	KK 3.96mm Crimp Terminal Housing, Friction Ramp, 3 Circuits, Natural
Application	Power, Wire-to-Board
Product Family	KK Interconnect Systems
Product Name	KK 396
UPC	800753613782

#### Agency

CSA	LR19980
UL	E29179

#### Physical

Breakaway	No
Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester

Net Weight	1.053/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
KK 396 Vertical Breakaway Headers	<u><a href="#">41661</a></u>
KK 396 Right-Angle Breakaway Headers	<u><a href="#">41662</a></u>
KK 396 Vertical Square Pin Breakaway Headers	<u><a href="#">41671</a></u>
KK 396 Right-Angle Friction Lock Breakaway Headers	<u><a href="#">41672</a></u>
KK 396 Vertical Headers with Friction Lock	<u><a href="#">41791</a></u>
KK 396 Right-Angle Headers with Friction Lock	<u><a href="#">41792</a></u>

### Use with Part(s)

Description	Part Number
Pre-Crimped Lead KK Plus 396 Female-to-KK Plus 396 Female, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Black	<u><a href="/content/molex/molex-dot-com/us/en/products/product-page.html/797582145.html">/content/molex/molex-dot-com/us/en/products/product-page.html/797582145.html</a></u>
Pre-Crimped Lead KK Plus 396 Female-to-KK Plus 396 Female, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Black	<u><a href="/content/molex/molex-dot-com/us/en/products/product-page.html/797582146.html">/content/molex/molex-dot-com/us/en/products/product-page.html/797582146.html</a></u>
KK 396 Female Crimp Terminals	<u><a href="#">2478</a></u>
KK 396 Female Crimp Terminals	<u><a href="#">2578</a></u>
Female Crimp Terminals for 3.96mm Pitch Housings	<u><a href="#">45570</a></u>

KK Trifurcon Female Crimp Terminals	<u>6838</u>
KK Trifurcon Female Crimp Terminals	<u>7258</u>

---

This document was generated on Sep 14, 2023