



Sample photo

**Order symbol:** CAB P 302017  
**Product nbr:** 8104303  
**Description:** Polyester cabinet  
**Remarks:** Grey door

**EAN:** 6418074050007  
**El. number:**  
 Finland 3424133  
 Denmark 8212018002  
 Sweden 2539817

**Including:** Cabinet base, door with PUR gasket, 3mm double bit lock(s) with transport and plastic key, screws for mounting plate/DIN-rail and wall fastening lugs with screws. Wall mounting screws not supplied.

Dimensions:			Rating:
L	W	H	
mm:	300	200	<b>Ingress Protection (EN 60529):</b> IP 66
inch:	11.8	7.9	<b>Impact Resistance (EN 50102):</b> IK 10
Materials:			Electrical insulation: Totally insulated
<b>Material:</b>	GRP		<b>UV resistance:</b> UL 508
<b>Base colour:</b>	RAL 7032		<b>Flammability Rating (UL 746 C 5):</b> UL 94 5V
<b>Cover colour:</b>	RAL 7032		<b>Glow Wire Test (IEC 695-2-1) °C:</b> 960
<b>Cover screws material:</b>	Stainless steel		<b>UL Type:</b> UL TYPE 3, 3R, 3S, 4, 4X, 12, 13
<b>Gasket material:</b>	Polyurethane		Certificates:
Temperatures:			
<b>Short term:</b>	-50 ... 150 °C		
<b>Continuous:</b>	-40 ... 70 °C		
<b>Short term:</b>	-60 ... 302 °F		
<b>Continuous:</b>	-40 ... 158 °F		
Accessories:			
MP 3020	Mounting plate		

