



Main

Range of product	Acti 9
Product or component type	Undervoltage release
Device short name	IMN
[Uc] control circuit voltage	48 V AC 50/60 Hz 48 V DC
Control type	Standard
9 mm pitches	2



Complementary



Range compatibility	Acti 9 iC65 Acti 9 ARA Acti 9 iDPN Vig Acti 9 iLD Acti 9 iSW-NA Acti 9 RCA Acti 9 iDPN (China version) Acti 9 iC60 double terminals miniature circuit breaker Acti 9 iC40
Local signalling	Action indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Width	18 mm
Colour	White
Connections - terminals	Clamp terminal - 1 cable(s) 9 mm ² - rigid Clamp terminal - 2 cable(s) 2.8 mm ² - rigid Clamp terminal - 1 cable(s) 7 mm ² - flexible Clamp terminal - 2 cable(s) 2.8 mm ² - flexible with cable end
Tightening torque	1 N.m
Compatibility code	IMN

Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins