




---

 PRODUCT-DETAILS

# AT21/M20/SA/BLY

## STR SWL PA66/NPB FTG M20 21MM-BLY




---

**General Information**

Extended Product Type	AT21/M20/SA/BLY
Product ID	7TCA296170R0275
EAN	5020963038129
Catalog Description	STR SWL PA66/NPB FTG M20 21MM-BLY
Long Description	Adaptalok ATS, Straight Conduit Fitting, Swivel External Male Thread, Nominal Conduit Size 21mm, M20 Thread, Polyamide (Nylon) 66, Nickel Plated Brass Thread/TPE, Black with Yellow Elastomer

---

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

---

**Ordering**

EAN	5020963038129
UPC	786210282299

---

**Technical**


---

Number of Batteries	0
Color	Black/Yellow Elastomer
Material	Polyamide/Nylon 6.6
Size	NC 21mm

---



---

**Environmental**


---

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---



---

**Container Information**


---

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963038129
Package Level 1 Height	9.84 in 250 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

---



---

**Certificates and Declarations**


---

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---



---

**External Classifications and Standards**


---

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
ETIM 9	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

---



---

**Categories**


---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

