

## Connection hoses - Male swivel connections



### Technical characteristics

**Construction:** Rubber with metallic braiding

**Highlight:** Resistant to oils, abrasion and ozone

**Equipped with:** Rotating coupling

BSPT male thread	Length (m)	Bend radius (at 20°C)(mm)	Max operating pressure (bar)	Temperature (°C)	Parts Numbers
R 3/8	1.5	130	180	-40 to +110	<b>LEM 17</b>
R 1/2	1.5	180	160	-40 to +110	<b>LEM 21</b>
R 3/4	1.5	240	105	-40 to +110	<b>LEM 27</b>
R 1	1.5	300	80	-40 to +110	<b>LEM 34</b>
R 1 1/4	2.2	420	63	-40 to +110	<b>LEM 42</b>
R 1 1/2	2.5	500	50	-40 to +110	<b>LEM 49</b>
R 2	2	630	80	-40 to +110	<b>LEM 60</b>