

# German standard plugs and extensions



Pack	Cat.Nos	
	Bulk	Gencod labelling
25	0 504 51	0 501 81

**2P plug - 16 A - rubber**  
 For the supply of class II devices  
 2 x 1.5 mm<sup>2</sup> max. cable  
 ● Black - straight outlet

Pack	Cat.Nos	
10	Bulk	Gencod labelling
	0 503 42	0 501 96
10	0 503 40	
10	0 502 52	0 969 29
10	0 503 43	0 501 97
10	0 503 44	0 501 98
10	0 503 41	
5	0 513 66	
5	0 513 69	

**2P+E plugs - 16 A and extensions - rubber**  
 Screw terminals  
 IK 08 - H07 RNF 3G 2.5 mm<sup>2</sup> max. cable

**Plugs**  
 ● Black - IP 44, screw cable grip  
 ● Black - IP 44 + cable gland  
 Robust gland-type cable grip which guarantees weatherproofing and tightening without tools. Optimum hold with traction of the cable grip: 30 kg at 2.5 mm<sup>2</sup> max.  
 ● Black - Side outlet with ring, screw cable grip

**Extensions**  
 ● Black, screw cable grip  
 ● Black - IP 44 with cap and plug inserted, screw cable grip  
 ● Black + cable gland  
 Robust gland-type cable grip which ensures weatherproofing and tightening without tools. Optimum hold with traction of the cable grip: 30 kg at 2.5 mm<sup>2</sup> max.  
 ● Black - 3 x 2P+E - IP 44 - with caps  
 ● Black - 3 x 2P+E - IP 44 - with caps and plugs inserted

Pack	Cat.Nos	
30	Gencod labelling	0 501 62
15	0 501 66	
30	0 501 63	
30	0 501 64	
30	0 501 65	
30	0 503 12	
30	0 503 14	
30	0 503 13	
15	0 503 05	
15	0 503 06	

**2P plugs and extensions - plastic - with extraction ring**

**6 A**  
 ○ Plug - White  
 ○ Extension - White  
 ● Plug - Black  
 ● Plug - Bronze  
 ○ Plug - Aluminium

**10 A**  
 ○ Plug - White  
 ● Plug - Black  
 ● Plug - Bronze  
 ○ Extension - White  
 ● Extension - Black

Pack	Cat.Nos	
15	Gencod labelling	0 501 83
15	0 501 84	

**2P plugs - 16 A - extra-slim - plastic**  
 Side outlet plugs, ideally behind an item of furniture  
 2 x 1.5 mm<sup>2</sup> max. cable, screw cable grip  
 ○ White  
 ● Black

Pack	Cat.Nos	
25	Bulk	Gencod labelling
	0 503 15	0 501 87
25	0 503 16	0 501 88
15	0 503 17	0 501 89
25	0 501 77	
25	0 501 78	
15	0 501 79	

**2P+E plugs - 16 A and extensions - plastic**  
 ○ Straight outlet plug - White  
 ○ Side outlet plug - White  
 ○ Straight outlet extension - White  
 ● Straight outlet plug - Black  
 ● Side outlet plug - Black  
 ● Straight outlet extension - Black

Pack	Cat.Nos	
25	Bulk	Gencod labelling
	0 503 24	0 501 92
10	0 503 25	0 501 93
25	0 503 30	0 501 90
10	0 503 31	0 501 91
25	0 503 28	0 501 94
10	0 503 29	0 501 95

**2P+E plugs - 16 A and extensions with rings - plastic**  
 3 x 2.5 mm<sup>2</sup> max. cable, screw cable grip  
 ● Plug - Grey  
 ● Extension - Grey  
 ○ Plug - White  
 ○ Extension - White  
 ● Plug - Black  
 ● Extension - Black

Pack	Cat.Nos	
4	Sleeve	0 501 99

**2P+E extension - 16 A - plastic - side outlet**  
 ○ White/Grey  
 Removable accessory packaging enabling attachment

Pack	Cat.Nos	
5	Gencod labelling	0 501 75
5	0 501 76	

**2P+E plugs - 16 A - easy extraction - plastic**  
 System enabling extraction of sockets thanks to the lever-extractor  
 3 x 1.5 mm<sup>2</sup> max. cable, screw cable grip, side outlet  
 ○ White  
 ● Black and Grey

Pack	Cat.Nos	
10	Gencod labelling	0 501 72
10	0 501 73	

**2P+E plugs - 16 A - cable orientation - plastic**  
 3 x 0.5 mm<sup>2</sup> max. cable, screw cable grip.  
 Enables the cable to be moved to 360°  
 ○ White  
 ● Black and Grey

**NEW**

## German standard multi-socket plugs and extensions



0 506 56



0 503 77

Pack	Cat.Nos	2P multi-socket plugs - 6 A
		For connection onto 2P+E socket Max. admissible power: 3.680 W at 230 V~
10	Cardboard 0 506 50	<b>4 side outlets</b> ○ White
10	0 506 51	● Black
10	Sleeve 0 506 55	<b>2P+E multi-socket plugs - 16 A</b> Max. admissible power 3.680 W at 230 V~ <b>2 front outlets</b> ○ White/Grey
10	0 506 56	<b>3 front outlets</b> ○ White/Grey <b>2 side outlets</b> With extraction button for easy disconnection of the plugs
5	Cardboard 0 506 65	○ White/Grey
10	0 506 62	<b>3 side outlets</b> ○ White
10	0 506 63	○ Transparent
5	0 503 77	<b>Multi-socket "octopus" extension leads ready to use - rubber</b> ● Black - 2P+E - 16 A - IK 10 With 1 plug and 3 extensions H07 RNF 3G 1.5 and 2.5 mm <sup>2</sup> cable Length: 0.8 m

## British standard plugs and TV plugs



0 503 26






6 500 13



6 500 15



0 500 10

Pack	Cat.Nos	British standard plugs
20	0 503 26	 13 A - 250 V~ - 2P+⊥ with CE marking
20	<b>NEW</b> 6 500 13	 13 A - 250 V~ - 2P+⊥ - without CE marking
20	6 500 15	 15 A - 250 V~ - 2P+⊥ - without CE marking
50		<b>TV plugs</b> ø9.52 mm Male plug
50	0 500 09	Female plug