



Years Warranty*

ANSMANN Powerbank 10000 mAh PB115PD MagSafe

Compact power bank with 10000 mAh capacity for wireless charging via MagSafe; additionally equipped with a USB-C port with Power Delivery (PD)

Features

- 10000 mAh Kapazität
- Kabelloses Laden mit bis zu 15 W
- Qi-kompatibel, inkl. MagSafe
- zusätzlicher USB-C Ausgang mit Power Delivery
- Status und Kapazitätsanzeige mit 5 LEDs



Article number: 1700-0199

Product content: Powerbank, USB-C cable, manual



Specifications

Nominal voltage	3,7 V			
Ports	1			
Cell chemistry	Lithium polymer			
Nominal capacity	10000 mAh			
Charging currents	Mode	Voltage range	Max. current	Max. power
	Wireless			15,0 W
	Wireless + USB C	5	3,0 A	15,0 W
	USB C	5	3,0 A	15,0 W
	USB C	9	2,2 A	20,0 W
	USB C	12	1,7 A	20,0 W
	PPS	5 - 5,9	3,0 A	17,7 W
	PPS 2	5 - 11	2,0 A	22,0 W
Output ports	USB type C / Wireless			
Input ports	USB type C			
Energy	38,5 Wh			
Maximum power	20 W			
Color	anthracite			
Operating temperature	10 - 35 °C			
Storage temperature	-20 - 25 °C			
Dimensions	97 × 64 × 17 mm			