



Datasheet

RS PRO18" High Velocity Floor Fan (BS&,VDE version)

EN



RS Article	Global Description
1792262	18" High Velocity Floor Fan , BS Plug
1792263	18" High Velocity Floor Fan ,VDE Plug

Contents:

Material: steel

Finished: chrome

230V-50HZ, 110W

Metal blade in chrome

Metal grill in chrome

rspro.com

Feature:

Rotary switch 3 speed

Speed 1: 7.77m/s

Speed 2: 8.43 m/s

Speed 3: 9.01m/s

Airflow :70/80/100 m³/min

32-33 radial guard

U shape base

This 3-in-1 fan features internal oscillation that creates a powerful wide

Energy saving motor, quiet performance

Provides unique and safe operation

Powerful airflow cools and ventilates fast

Wide blowing angel allows for wider room coverage

GS /CE approval

