
268 - Round crowbars with crook beak

[]



Description:

• Forged, one spindle end and one wide and slim pallet end, hardened to 45 HRc.

• Presentation: red lacquered, polished, varnished ends.



	Length L [mm]	Length L1 [mm]	Thickness E [mm]	Weight [Kg]
268.3	450.0	32.0	16.0	0.67
268.4	790.0	32.0	20.0	1.97
269	400.0	27.0	18.0	0.59