

Plug screw
NETC-P-M20-PBK-T26-EX4-E
Part number: 8151589

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Ambient temperature	-40 °C ... 75 °C
Degree of protection	IP66 IP68
Note on degree of protection	IP68 at 5 bar for 30 minutes
ATEX category gas	II 2G
ATEX category dust	II 2D
Explosion ignition protection type for gas	Ex eb IIC Gb
Explosion ignition protection type for dust	Ex tb IIIC Db
Explosion ambient temperature	-40°C ≤ Ta ≤ +75°C
Explosion protection certification outside the EU	EPL Db (IEC-EX) EPL Gb (IECEX)
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX) In accordance with EU RoHS Directive
Size	M20x1.5
Colour	Black
Material cable gland	PA
Material seals	EPDM
Product weight	5 g
Size of pack	1
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant