

INSULATED TORQUE SCREWDRIVER SET FOAM3 27 PIECES



- Approved for live working up to 1,000 volts
- Integrated protective insulation with two colours clearly indicate if there is any damage
- Tools are hold in place using three colour pre-cut high-density EVA foam clearly showing where each tool belongs
- Design to fit exactly in the TengTools service cases
- Design and manufactured to IEC60900 (EN60900)
- Organised in a foam inlay module size 3 (FOAM3)

Insulated Socket and Torque Screwdriver Set 27pcs

General information

Country of origin: Taiwan
Barcode: 5020385011618
Tarriff code Europe: 8205400000
ECCN US: EAR99
ETIM: EC011815
UNSPSC: 27113201

Dimensions

Net weight (g): 1651
Width (mm): 433
Depth (mm): 267
Height (mm): 49

Attributes

Product type: Insulated Tool Sets
Certificates: N/A
Number of pieces: 27
Handle type: Bi-material
Insulated: Yes
Inlay material: FOAM
Type of set: FOAM3

Features



**FOAM
SERIES**



Technical changes and errors may occur. 01-08-2024 19:59



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden

LIST OF CONTENTS



TEFXV27 Insulated Torque Screwdriver Set FOAM3 27 Pieces

1492TVSD	Insulated Torque Screwdriver 1-5Nm
MDV731	Interchangeable Blade Insulated Screwdriver 3 mm
MDV732	Interchangeable Blade Insulated Screwdriver 4 mm
MDV733	Interchangeable Blade Insulated Screwdriver 5.5 mm
MDV734	Interchangeable Blade Insulated Screwdriver 6.5 mm
MDV751	Interchangeable Blade Insulated Screwdriver PH1
MDV752	Interchangeable Blade Insulated Screwdriver PH2
MDV771	Interchangeable Blade Insulated Screwdriver PZ1
MDV772	Interchangeable Blade Insulated Screwdriver PZ2
MV3800	3/8" Insulated Ratchet 72 Teeth
MV380020	3/8" Insulated Extension Bar 75 mm
MV380021	3/8" Insulated Extension Bar 150 mm
MV380506	3/8" Insulated Socket 6 mm
MV380507	3/8" Insulated Socket 7 mm
MV380508	3/8" Insulated Socket 8 mm
MV380509	3/8" Insulated Socket 9 mm
MV380510	3/8" Insulated Socket 10 mm
MV380511	3/8" Insulated Socket 11 mm
MV380512	3/8" Insulated Socket 12 mm
MV380513	3/8" Insulated Socket 13 mm
MV380514	3/8" Insulated Socket 14 mm
MV380515	3/8" Insulated Socket 15 mm
MV380516	3/8" Insulated Socket 16 mm
MV380517	3/8" Insulated Socket 17 mm
MV380518	3/8" Insulated Socket 18 mm
MV380519	3/8" Insulated Socket 19 mm
MV380520	3/8" Insulated Socket 20 mm