



Features

• The streamlined, durable, lightweight die-cast aluminium body makes SylFlood a perfect choice for building facades, car parks, garages and construction areas. The product includes 1 m pre-wired stripped cable and fitting bracket for quick and easy installation and the universal mounting bracket allows wall or surface mounting with the possibility of vertical tilting. White (RAL9003) housing, white reflector, 3000 lm, 26 W, 115 lm/W, 4000K, non dimmable, CRI>80, IP65, IK06, Class I, 112 x 125 x 26 mm (L x W x H). Weight: 0.325 kg.

Product Overview

Product name	SylFlood IP65 3000LM 840 White
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Floor standing
General application	Retail
ETIM Class	EC001744
Fixture luminous flux (lm)	3000
Luminaire efficacy (lm/W)	115
Correlated colour temperature (k)	4000
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam Angle (°)	110
Photobiological Risk Group	RG1
Total power consumption (W)	26
Electrical protection	Class I
Control gear type	Not required



SylFlood IP65 3000LM 840 White
0090157

Dimmable	No
Housing colour	White
IP rating	IP65
IK rating	IK06
Product EAN number	5410288901572
Warranty	3 years
Dimming method	N/A