

## Rexel Optimum AutoFeed+ 225X Automatic Cross Cut Paper Shredder

The Optimum AutoFeed+ 225X cross cut shredder automatically shreds up to 225x A4 sheets of paper (80gsm) at a time, into P-4 (4x25mm) cross cut pieces. This auto feed shredder machine is a sophisticated office shredder, featuring a 60L pull out bin. No need to manually feed paper, or remove staples and paper clips first, this automatic paper shredder will do all the work for you.



## Attributes

- Auto feed up to 225 sheets of A4 paper (80gsm) at a time. Manual slot for up to 10 sheets.
- P-4 cross cut (4x25mm)
- 60L capacity pull out bin. Castor wheels for ease of movement around the workplace.
- Anti-jam technology
- Shreds credit cards, staples and paper clips.
- 30 minutes continuous run time with fan cooling. Sleep mode activates after 3 minutes of non use.
- Touch control panel
- 55 dBA ultra-quiet noise level
- Infra red bin full sensor
- 2 year warranty, 2 year cutter warranty



## Specifications

Number	2020225X
Colour	black
Dimensions (W x H x D)	415 x 806 x 465 mm
Cut Type	Cross Cut
Maximum Slot Entry Width (mm)	230
Run Time From Cold (min)	30
Shredded Particle Width mm	4x25
Security Level	P-4
Cutting Capacity sheets (70gsm paper)	248
Cutting Capacity sheets (80gsm paper)	225
Container/collection volume in l	60
Shreds	Paper, Credit cards, Paper clips & Staples
Power consumption (W)	400
Noise Level (dBA)	55
Period of Warranty (Years)	2
Location	Office
Number Of Users	5-10
Weight	22000 g
Pallet quantity	4
EAN code	5028252606271