

▶ **PVC-coated series**

PVC model

149.Y

- Length 155 mm.
- ΔΔ : 25 g.



Gripping model

146.1Y

- Ø 2.5 to 4 mm in-line grip.
- Length 140 mm.
- ΔΔ : 25 g.



PVC model

152.Y

- Length 150 mm.
- ΔΔ : 25 g.



Gripping model

146.2Y

- Ø 2.5 to 4 mm right-angle grip.
- Length 140 mm.
- ΔΔ : 25 g.



▶ **High-precision series**

141 Straight models

- Non-serrated easy-flex snipe tips.

➤	Length mm	ΔΔ g
141.11	110	13
141.12	120	14



Offset model at 15

142.2

- Non-serrated easy-flex snipe tips.
- Length 117 mm.
- ΔΔ : 15 g.



Ultra-flat straight model

144

- Finely contoured, non-serrated tips.
- Length 120 mm.
- ΔΔ : 17 g.



Straight shouldered model

142.1

- Non-serrated easy-flex snipe tips.
- Length 112 mm.
- ΔΔ : 13 g.



Curved model

143

- Non-serrated easy-flex snipe tips.
- Length 114 mm.
- ΔΔ : 14 g.



Splayed straight model

145

- Non-serrated tips.
- Tip width 7 mm.
- Length 123 mm.
- ΔΔ : 14 g.

