

tesa® Professional 60399



Product Information

Plastering Tape

tesa® 60399 is a plasticized PVC tape with low unwinding force and medium adhesion with a flat film. Having a rubber adhesive coating, tesa® 60399 is suitable for most surfaces. Once applied, the tape can withstand humidity, weak alkaline solutions, acids and many other chemicals.

Main Application

Masking applications during plastering both as bundling and fixation jobs can be performed with this quality.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Technical Data

• Backing material	soft PVC	• Elongation at break	170 %
• Total thickness	120 µm	• Tensile strength	22 N/cm
• Type of adhesive	natural rubber	• UV-resistance	2 weeks

Adhesion to

- steel 2.0 N/cm

Properties

• Hand tearability	●●●	• Sharp color edge	●●●
• Suitable for rough surfaces	●●●●	• Conformability	●●●●
• Paint anchorage	●●		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

Additional Information

The tape can be used for temperatures above 5°C.

tesa® Professional 60399

Product Information



Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=60399>