



DCS387NT

18V XR Li-Ion Compact Reciprocating Saw - Bare Unit

Selling Proposition

- Compact saw allows better access to hard to reach cuts
- Improved balance and ease of handling due to central motor position
- Four position blade clamp allows for flush cutting and improved versatility
- Lever action keyless blade clamp for tool-free blade change
- LED for improved visibility of cut
- Includes heavy-duty TSTAK II kitbox

Standard Equipment

- TSTAK II heavy-duty kitbox
- Battery and charger sold separately

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Output	610 Watt
No Load Stroke Rate	0 – 2900 spm
Stroke Length	28.6 mm
Weight	2.3 kg