



DEWALT 18V XR Cordless Fan

DCE512N-XJ



- Durable cordless fan provides high airflow and air speed of 28 m³/min, for increased cooling effect
- 180° pivoting fan head allows for versatile positioning, saving time and effort positioning fan
- Variable speed setting for adjustable airflow rate
- Convenient hang hooks provides greater versatility when positioning fan
- Extended runtime of up to 4 Hours on Max using a 5Ah battery
- Compatible with 18V XR and XR FLEXVOLT battery range

Description:

The DEWALT 18V XR fan offers the options you need on the jobsite, with a powerful high airflow and air speed of 28 m³/min, for increased cooling effect. Stand it up, hang it, or mount it where you need, so it's not in the way. The 180° pivoting fan head allows for versatile positioning, saving time and effort positioning fan. The variable speed control, allows you to adjust the flow rate so you can set the power you want. Battery and charger sold separately.

What we like - Compact powerful fan with multiple positioning options with extended runtime.

Supplied With:

• Naked fan only.

Specifications	
Battery	XR Lithium-Ion
Voltage	54/ 18 V
Airflow	28 m³/min
Fan speed	3000 rpm
Blade size	178mm
Speed settings	Variable (dial)
Noise	62dB
Fan head tilt	180°
Weight	3.4 kg