

Datasheet

RS Pro Straight 75Ω Cable Mount BNC Connector Plug, Twist On Termination RG59 Nickel

RS Stock No: **546-5008**



Product Details

RS Pro straight cable mount BNC connector plug features a nickel plated body, washers, gold plated centre contacts and is for use with a variety RF coaxial cable types. This male connector plug has 75 Ω impedance. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Nickel plated body, washers, gold plated centre contacts
- Twist on termination method
- Male connector
- Suitable for a variety of applications including video signalling and test equipment

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Cable Type	RG59
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	75 Ω
Mounting Type	Cable Mount
Operating Frequency	1 GHz
Polarity	Normal
Termination Method	Twist On
Operating Temperature Range	-20 to +60°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)