

ABSU 12 C

2-speed cordless drill/driver

Order number:: 7 113 20 64 00 0

FEIN SELECT⁺



Powerful and light cordless drill/driver with fixed drill chuck.

- Powerful and long-life DC motor with overheating and overload protection.
- Robust solid metal drill chuck with chucking force safety device.
- Short design of 180 mm.
- Perfect for use with stepped drill bit, e.g. for drilling initial holes in sheet metals.
- 17 torque levels – force can be easily metered up to 20 Nm for tough screw connections.
- 2-speed solid metal gearbox.
- Bright LED light on housing.
- 2.5 Ah battery capacity for up to 350 screw connections (5 x 40 mm).
- FEIN SafetyCell technology. Protects the battery and tool from overload, overheating and total discharge.
- The battery charge can be read off the battery.
- Includes belt holder and magnetic bit holder.
- One charger for all FEIN Li-ion batteries of all voltage classes.



ABSU 12 C

2-speed cordless drill/driver

Order number:: 7 113 20 64 00 0

Technical data

Battery voltage	12 V
Motor	2-pole DC
Gearbox	2-speed
Speed, no load	400 / 1 300 rpm
Max. torque (hard/soft)	20 / 14 Nm
Torque levels	17 + 1
Drill chuck clamping width	1 - 10 mm
Fastening	6 x 200 mm
Capacity in steel Ø	10 mm
Capacity in wood Ø	30 mm
Cordless	X

Included in price::

- 1 cordless drill/driver
- 1 belt clip
- 1 bit holder
- 1 plastic carrying case