

612328110

Aluminium Enclosure Standard unpainted 230 x 280 x 111 mm

Aluminium Enclosure Standard unpainted
230 x 280 x 111 mm

Declaration of Conformity

Technical Drawing | 3D Data | Assignmentplan | Terminal mounting

Technical data

Height	230 mm
Width	280 mm
Depth	111 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AlSi 12 (Fe)
Colour	Aluminium, unpainted
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
Temperature min.	-30 °C
Temperature max.	90 °C
Seal material	CR-(Chloropren)
Flame spread, sideways	HL 3
Rate of heat dispersion	HL 3
Smoke gas concentration	HL 3

ROSE Systemtechnik GmbH

Commercial data

Country of origin	DE
Order unit	1 Piece
Customs tariff number	85369095
Weight	3.2 kg
GTIN	4250157900326

ETIM Classification

ETIM 8	EC000058

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



100110160
Mounting plate for 01.232811



100220010
Hinge internal / Steel



100270010
Hinge internal / Grey



100311020
Outer bracket fastening set M6



100614310
DIN rail 35/7,5 for xx.232811



100620090
Earth rail for 01.232811