



ENGLISH

T4507EP - 24Vac Single Output Weatherproof Power Supply



Specifications:

- 230Vac input (European)
- 24Vac Output
- IP Rated Weatherproof unit
- Class I power (required to be earthed)
- Wall-mountable
- Suitable for use in security applications & many others.





ENGLISH

Characteristics	
Manufacturers Part Number	T4507EP
RS Stock Code	1244715
Voltage	24VAC
Voltage (No load)	27.2VAC
Current Max	7A
Power (VA)	168VA
Protections	F8A 20x5mm Quick Blow Glass Fuse
Weight	<2.5Kg
Output Connection Style	Re-Wireable Terminal block for 24Vac Output
Rated Input Voltage	230VAC +/- 10%
Magnetising Current	45mA
Rated Frequency	50Hz
Input Fuse	T3.15A 20x5mm Time Delay Glass Fuse
Flash Test	4KV
AC Input Connections	Re-Wireable Terminal block for L - E - N wires
Operating Temperature	0C to 40C
Storage Temperature	-10C to 70C
Operating Humidity	20 to 80%
Storage Humidity	10 to 90%
Safety Approvals	CE Complaint
EMI Standards	EMC Compliant
PB-Free	Yes. RoHS Compliant
MTBF	50K Hours
Weatherproofing	IS65/IP66