

Inductive Sensors



Housing Style	Part Number	ID Number	Features	Sensing Range (mm)	Output
12 mm - Nonembeddable, eurofast® Connection 	Ni 4-M12-AD4X-H1141	T4406700		4	2-Wire DC
	Ni 4-M12-AD4X-H1144	M4406701		4	
	Ni 8-M12-AD4X-H1141	T4411241	Ext. Range	8	
	Ni 8-M12-AD4X-H1144	T4411289	Ext. Range	8	
	Ni 4-EM12-AN7X-H1141	T4606893	TTL Compatible	4	3-Wire DC NPN
	Ni 4-M12-AN6X-H1141	T4606800		4	
	Ni 5-M12-AN6X-H1141	T4671390		5	
	Ni 8-M12-AN6X-H1141	T4611315	Ext. Range	8	
	Ni 8U-EM12-AN6X-H1141	M1644350	Uprox	8	
	Ni 8U-M12-AN6X-H1141	M1644150	Uprox	8	
	Ni 8U-M12-AN6X2-H1141	M1644155	Uprox, Dual LED	8	
	Ni 10U-EM12-AN6X-H1141	M1634828	Stainless Steel	10	
	Ni 10U-M12-AN6X-H1141	M1634826	Stainless Steel	10	3-Wire DC PNP
	Ni 4-M12-AP6X-H1141	T4606700		4	
	Ni 5-M12-AP6X-H1141	T4653400		5	
	Ni 8-M12-AP6X-H1141	T4611310	Ext. Range	8	
	Ni 8U-EM12-AP6X-H1141	M1644340	Uprox	8	
	Ni 8U-M12-AP6X-H1141	M1644140	Uprox	8	
	Ni 8U-M12-AP6X2-H1141	M1644145	Uprox, Dual LED	8	
	Ni 10U-EM12-AP6X-H1141	M1634808	Stainless Steel	10	
	Ni 10U-M12-AP6X-H1141	M1634806	Stainless Steel	10	4-Wire DC NPN
	Ni 4-M12-VN6X-H1141	T1643100	Comp. Output	4	
	Ni 8-M12-VN6X-H1141	T4611323	Ext. Range, Comp. Output	8	4-Wire DC PNP
	Ni 4-EM12-VP6X-H1141	M1633101	Comp. Output	4	
	Ni 4-M12-VP6X-H1141	T1633100	Comp. Output	4	
	Ni 8-M12-VP6X-H1141	T4611324	Ext. Range, Comp. Output	8	
	Ni 5-M12-Y1X-H1141	M4010300		5	2-Wire DC NAMUR

For detailed sensor specifications see Section M.
Normally Closed versions available upon request, consult factory.



Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection	Housing	Face	Power LED	Output LED	Mating Cordset	Wiring Diagram #	Wiring Diagrams
10-65 VDC	2000	≤100	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.2T-*	1	Diagram 1
	2000	≤100	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.23T-*	2	
	2000	≤100	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.2T-*	1	Diagram 2
	2000	≤100	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.23T-*	2	
10-30 VDC	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RKV 4T-*	3	Diagram 3
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	3	
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RKV 4T-*	3	
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	3	
	2000	≤200	-30 to +85	IP 68	SS	PA 12	N/A	YE	RKV 4T-*	3	Diagram 4
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	3	
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	GN	YE	RK 4T-*	3	
	1000	≤200	-30 to +85	IP 68	SS	LCP	N/A	YE	RK 4T-*	3	
10-30 VDC	1000	≤200	-30 to +85	IP 68	CPB	LCP	N/A	YE	RK 4T-*	3	Diagram 5
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	4	
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RKV 4T-*	4	
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	4	
	2000	≤200	-30 to +85	IP 68	SS	PA 12	N/A	YE	RKV 4T-*	4	Diagram 6
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	4	
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	GN	YE	RK 4T-*	4	
	1000	≤200	-30 to +85	IP 68	SS	LCP	N/A	YE	RK 4T-*	4	
10-30 VDC	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	5	Diagram 7
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	5	
10-30 VDC	2000	≤200	-25 to +70	IP 67	SS	PA 12	N/A	YE	RKV 4.4T-*	6	Diagram 7
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	6	
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	6	
5-30 VDC	2000	Remote	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.21T-*	7	

* Length in meters.

For material descriptions see page M36.