




NO	DESCRIPTION	DATE
⚠	ADD MIS PART NO.	04.01.04
⚠	ADD DESCRIPTION ADD 6.2±0.38 24.99±0.13 → 24.99±0.25 16.33±0.13 → 16.33±0.25 ø3.05 → ø3.05±0.25 7.9 → 7.9±0.25 12.55 REF. → 12.55±0.38 2.77 → 2.77±0.38 19.28 REF. → 19.28±0.38 1 → 0.76±0.25 10.72 REF. → 10.72±0.38 11 REF. → 10.85±0.38 3.3 REF. → 2.4±0.5 2.84 → 2.84±0.38 TIN → GOLD MIS PART NO. → P/N	10.02.07
⚠	CORRECT DIMENSION LINE POSITION	12.02.11
⚠	GOLD	05.16.13

CONTACT TYPE
COLOR OF INSULATION
PLATING OF CONTACT
SOLDER TERMINATIONS
WORKING VOLTAGE
CONTACT RESISTANCE
MATING CYCLES

MACHINED CONTACT
BLACK PBT GLASSFIBRE REINFORCED
⚠ GOLD
⚠ GOLD
500V AC AT SEA LEVEL
10m OHM MAX.
150 TIMES



⚠ P/N:544-3755

APPROVED

by _____ DATE: _____



DESCRIPTION		D-SUB WITH 9-PIN FEMALE CONNECTOR BY MACHINING							
製圖	DRAWN	TOLERANCE		品名	050-0009S-M	日期	DATE	版次	REV.
	Yoko	.X	±0.2	TITLE	\ROHS COMPLIANT	03.06.08			A-4
檢圖	CHECK	.XX	±0.1	單位	mm(in)	DWG.NO. 55-0045			
	Ivan	.XXX	±0.05	SCALE					
認定	APPROVAL	ANGLE	±5°	比例	2:1				
	Angela								