

## Features

- Versatile switch suitable for many heavy duty applications
- Compatible with all industry standard V3 switches.
- Available with solder, quick connect and screw terminals.
- Long mechanical and electrical life
- Fire Silver contacts.
- Temperature range upto 85°C
- Positive snap action.
- Conform to IEC 1058-1-standard

## RS PRO Micro Switch

RS Stock No.: 0241237



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Efficient motor variant designed for compact applications, featuring robust construction and reliable performance.

## General Specification

Actuator Type	Long Roller Lever
Terminal Type	Quick 1.75X0.5
Contact Current Rating	16 AMP
Contact Configuration	Solder Type
IP Rating	40
Operating Force	125 Gms
Minimum Operating Temperature	-55(°C)
Maximum Operating Temperature	85°C
Switch Housing	G.F PBT
Contact Material	COPPER ALLOY
Case Material	G.F PBT
Mechanical Life	100000
Voltage Rating	250V
Release Force	14 Gms
Switch Operation	Snap Action

<b>Standards Met</b>	CE AND CSA
<b>Applications</b>	Business and office machines Industrial Electronics Defence Power Sector

