

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: Intelligent Group Solutions Ltd

Supplier's address: 24hour Solutions B.V. , Van Nelleweg 1, 3044BC Rotterdam, NL

Model identifier: ILX-E507-WM10-3240-SD211

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	WIRES		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No


Product parameters

Parameter		Value	Parameter	Value
General product parameters:				
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer		104	Energy efficiency class	F
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)		11 200 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000
On-mode power (P_{on}), expressed in W		104,0	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal		-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	85
Outer dimensions without separate control gear, lighting control	Height	5	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
	Width	10		
	Depth	3 240		


parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-	
		Chromaticity coordinates (x and y)	0,433 0,396	
Parameters for LED and OLED light sources:				
R9 colour rendering index value	0	Survival factor	1,00	
the lumen maintenance factor	0,96			

(a) : not applicable;

(b) : not applicable;



Model placed on the Union market from 20/02/2023.



EPREL registration number: 2066392

<https://eprel.ec.europa.eu/qr/2066392>

Supplier: 24hour Solutions B.V. (Authorised representative)

Website: www.24hour-ar.com

Customer care service:

Name: 24hour Solutions B.V.

Website: <https://www.24hour-ar.com/>

Email: info@24hour-ar.com

Phone: +31 (0)10 321 21 16

Address:

Van Nelleweg 1
3044BC Rotterdam
Netherlands