




GTT P/N	MDP3SA	MDP4SA	MDP5SA	MDP6SA	MDP7SA	MDP8SA
RS P/N	463-366	463-372		463-388		463-394
No of pins	3	4	5	6	7	8



Rating: 100V AC 1A
Insulation Resistance: 50M ohm Min
Resistance: 50Mohm/500V DC
Dielectric: 500V AC/1minute
Temp range: -25°C to +85°C
Applicable wires:AWG 28 to 30

Materials:

- A.BOOT: PVC**
- B.MIDDLE HOOD: ABS**
- C.METAL PART: COPPER,Nickel Plated**
- D.INSULATOR: PBT or Nylon+30% Fiber reinforced(UL94Y-0)**
- E.Contact material:Brass Compound or Brass Alloy**

UNLESS OTHERWISE SPECIFIED TOLERANCE: L ±0.2 ANGLES: 27 LX ±0.1 LXX ±0.05 50 MM SCALE DRAWING				TITLE MINI DIN PLUG ASS'Y TYPE			
DRAWN BY ANDY	SIZE A	UNIT MM	PART NO. 463-3xx		PAGE 1 OF 1		
CHECKED BY <i>[Signature]</i>	SCALE 1 : 1	THIRD ANGLE PROJECTION 		DATE 08/27/2001			
APPROVED BY <i>[Signature]</i>	ITEM NO. MDPxSA						
DWG NO.							