

FEATURES

- Resolution: Metric 0.01mm.
- Micro fine graduations for accurate reading.
- Suitable for groove measurement
- Fixed and moving blades ground 0.75mm x 6.5mm

RS PRO External Micrometer, Range 0 mm - 25 mm DIN863

RS Stock No.: 180-9465



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Data Sheet

Product Description

Non-revolving spindle.
Blade anvils: 0.75mm wide. x 6.5mm long.
Spindle locking lever.
Ratchet stop.
Non-glare satin chrome barrel and sleeve.
Blue baked enamel hammer tone finish.
Supplied in fitted case with adjustment tools.

General Specifications

Resolution	0.01 mm
Imperial or Metric	Metric
Micrometer Type	External
Set Contents	Adjustment Tools, Fitted Case, Mechanical Blade Micrometer
Maximum Measurement	25mm
Minimum Measurement	0mm

Mechanical Specifications

--	--

Electrical Specifications

--	--

Protection Category

--	--

Classification

eCI@ss (Version)	
UNSPSC (Version)	



Data Sheet

Approvals

Declarations	
Hazardous Area Certification	
Standards Met	DIN863/2

Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories