

current transformer 600/5 A 5 VA CL 0.2s



Model	
Product brand name	SENTRON
Product designation	Current transformer
Design of the product	Bushing-type current transformers
Operating apparent output / rated value	5 V·A

Protection class	
Protection class IP	IP20
<ul style="list-style-type: none"> • Ratio of input current/output current • Current / at output / rated value • Current / at input / rated value 	600/5 5 A 600 A
Accuracy class / of the current transformer	Class 0.2s
Product feature / Touch protection	Yes

Connections	
Type of electrical connection / at output	screw-type terminals

Mechanical Design	
Height	78.5 mm
Height of the opening	30 mm
Width	60 mm

Width	
<ul style="list-style-type: none"> • of the push-through bus bar / at 1 bus bar / maximum 	30 mm
<ul style="list-style-type: none"> • of the push-through bus bar / in case of 2 bus bars / maximum 	30 mm
Depth	65 mm
Mounting type	screw fixing
Outer diameter / of the push-through conductor / maximum	26 mm
Net weight	453 g

Environmental conditions

Ambient temperature	
<ul style="list-style-type: none"> • during operation / minimum 	-30 °C
<ul style="list-style-type: none"> • during operation / maximum 	55 °C

Certificates

Reference code / acc. to DIN EN 61346-2	T
---	---

Declaration of Conformity



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4NC5227-2FE21>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4NC5227-2FE21>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=4NC5227-2FE21

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



