

FEATURES

- **Sintered Bronze Material:** Provides high durability and wear resistance.
- **Flanged Design:** Ensures secure positioning and easy installation.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads.
- **Bore Size of 38.03 mm:** Fits standard shafts for versatile use.
- **Outside Diameter of 48.06 mm:** Compatible with a wide range of housings.
- **Width of 25 mm:** Offers stability and support in applications.

RS PRO 38.03 mm Flanged Plain Bearing

RS Stock No: 558-497



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for reliable performance in various industrial applications. Made from sintered bronze, it offers excellent durability and resistance to wear. Ideal for use in machinery where low maintenance and high load capacity are required.

General Specifications

Bore Size	38.03 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	48.06 mm
Width	25 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

