



JetNet 3008G V2

Industrial 8-port Unmanaged GbE Switch

8 Gigabit Ethernet Ports with Auto MDI/MDI-X
 10K bytes Jumbo frame for large file transmission
 IEEE 802.1p Quality of Service (QoS) for packet forwarding precedence
 Broadcast storm packet filtering
 Dual DC 9~60V power inputs
 Port and power event alarm
 IP30 rugged aluminum case

Facts

General description

Part number	F00N3008000008
Life cycle status	Mature
Warranty	Up to 5 years

Interface

Total ports number	8
10/100/1000TX ports	8
DI/DO (dry relay)	1 relay DO with 1A/24VDC ability
DC power input	2 x DC 24V (9-60V)

Features

Switch type	Unmanaged
Broadcast storm protection	Yes

SW/Protocol

Traffic priority (QoS)	4 Queues
Jumbo frame/MAC address	10K Bytes
Event alarm	Port Alarm Power Alarm

Mechanical

Housing/protection (IP)	IP30/Metal
Dimension (HxWxD mm)	120 x 55 x 112
Mounting	DIN Rail
Operating temperature	-40~70°C

Certification

Regulatory/approval	CE/FCC/E-mark
RoHS	Yes

People & Technology. Connected.

We are a people company. Our experienced, skilled and passionate people empower you to meet your challenges through best-in-class, user-friendly solutions. We are a technology company. We help you optimize processes through our software, hardware and services, and through our support. Connecting people and technologies gives you the means to accomplish your goals and ambitions, and gain a competitive edge in today's digitalized world.

Visiting address HQ: Stora Varvsgatan 13a

SE - 211 75 Malmö, SWEDEN

[+46 40 35 86 00](tel:+4640358600) (tel:+46 40 35 86 00)

info@beijerelectronics.com (mailto:info@beijerelectronics.com)