


DL.BTI - Heavy duty series bottle jacks



Description:

- Capacity: 2t, 5t, 8t, 12t, 20t, 30t.
- Designed for heavy-duty professional use.
- Welded base plate jacks, control in the axis: Stronger, more stable, less leaks.
- Heat and surface treated pump shaft and actuator.
- Allows for horizontal use as a pusher jack.
- Complies with directive on machinery 2006/42/CE.

	A [mm]	Head Height C [mm]	Head Width B [mm]	Tonnes [t]	Weight [Kg]
DL.12BTI	238.0	80.0	160	12	8
DL.20BTI	270.0		160		
DL.2BTI	178.0	52.0	177	2	2,4
DL.30BTI	280.0		165		
DL.5BTI	198.0	70.0	122	5	3,7
DL.8BTI	198.0	72.0	124	8	5,6