



Welding high-quality glove with cut protection F, heat resistant up to 100°C /212°F.

## ■ TEGERA® WELDING 7787



[Learn more](#)

### WELDING GLOVE WITH HIGH CUT PROTECTION

Welding glove made from premium quality black goat grain leather with a cow split cuff reinforced with canvas. The high-quality materials offer a perfect fit and fleece inside makes the glove comfortable. Gun grip reinforcements provide added durability and grip, and control patches protect against both abrasion and heat. The glove has cut protection F with Kevlar® and is heat resistant up to 100°C /212°F. To enhance fingertip sensitivity, the glove features a unique folded fingertips design.

#### CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Extra flexible
- Very durable
- Excellent grip
- Perfect fit

#### FUNCTIONS

- Withstands contact heat up to 100°C
- Heat-resistant sewing thread
- Reinforced index finger
- Reinforced seams
- Reinforced fingers and thumb
- Reinforced thumb

**PREVENTS RISK OF**

Burn injuries, Heat injuries, Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations

**PRIMARY ENVIRONMENTS OF USE**

Cut risk environments, Warm environments

**PRIMARY AREAS OF USE**

Agricultural work, Airport work, Assembly, Building and construction, Chemical technology work, Concrete work, Construction, Electric power work, Electrical installation, Electronics work, Engineering, Fishing industry work, Forest work, Foundry, Gardening, Glass industry work, Healthcare, Hot work, Hunting, Inspection work, Installation work, Laboratory work, Machine driving, Machine operating, Metalwork, Military work, Mining, Office work, Paper industry work, Petro-chemical work, Repair work, Rescue work, Sanitation, Security- and police work, Service work, Sheet-metal work, Soil preparation, Transport work, Warehouse work, Welding, Wood industry work

**PRIMARY INDUSTRIES OF USE**

Agriculture, Mining, Oil, gas, petrochemical, Food processing, Pulp and paper, Chemical, Rubber and plastic, Glass, bricks, concrete, Metal fabrication, Machinery and equipment, MRO, Automotive, Transportation, Utilities, Building and construction, Logistics, HoReCa, Facilities, Retail

**TYPE OF WORK**

Heavy weight

**SPECIFICATION**

TYPE Welding gloves

CATEGORY Cat. III

COLLECTION Welding

PALM MATERIAL Full grain goatskin of top quality

BACK MATERIAL Full grain goatskin of top quality

LINING Fully lined

LINING MATERIAL KEVLAR® fiber

DEXTERITY 5

PAIRS PER: BUNDLE/CARTON 6/30

DISPLAY TYPE Hangtag with euro slot

FASTENING Elasticated 180°

CUFF STYLE Safety cuff

CUFF MATERIAL Leather

CUT RESISTANCE (EN ISO 13997) Cut resistance level F

CUT RESISTANCE (EN ISO 13997) TDM: 35.3 N

INNER MATERIAL SPECIFICATION Cotton

MIDDLE MATERIAL SPECIFICATION Cotton, Para-aramid

OUTER MATERIAL SPECIFICATION Leather

**COMPLIANCE**



EN ISO 21420:2020



EN 12477:2001+A1:2005

Type B



**Warning, this model is not intended for use in wet conditions**

**FEATURES**



SIZE		ARTICLE NUMBER	EAN
10	XL	7787-10	7340118484990
11	XXL	7787-11	7340118485140
12	3XL	7787-12	7333506002159
7	S	7787-7	7340118484549
8	M	7787-8	7340118484693
9	L	7787-9	7340118484846

**ejendals**

Limavägen 28, SE-793 32 Leksand, Sweden

Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com