

## Features

- Shock-Absorbing Tips: Polyurethane tips for controlled, non-marring strikes.
- Robust Build: Forged steel body ensures durability and long service life.
- Protective Collar: Nylon collar reduces wear and safeguards the mallet.
- Comfortable Grip: Varnished ash wood handle for ergonomic handling.
- Ideal for Delicate Work: Perfect for assembly, maintenance, and tasks requiring gentle impact.

## RS PRO Polyurethane Mallet with Forged Steel Body, Nylon Collar & Varnished Ash Handle, 30mm Head Diameter

RS Stock No.: 0747539



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*The RS PRO Polyurethane Mallet is engineered for precision and protection in industrial and workshop environments. Its polyurethane tips deliver non-marring strikes, making it ideal for delicate surfaces. The forged steel body provides strength, while the nylon collar adds extra durability. A varnished ash wood handle ensures comfort during prolonged use. This mallet is perfect for assembly, maintenance, and repair tasks where controlled force is essential.*

## General Specifications

|                 |                     |
|-----------------|---------------------|
| Product Type    | Polyurethane Mallet |
| Handle Material | Polyurethane        |
| Body Material   | Forged Steel        |
| Collar Material | Nylon               |
| Handle Material | Varnished Ash Wood  |
| Head Diameter   | 30 mm               |
| Overall Length  | 300 mm              |
| Head Length     | 85 mm               |
| Weight          | 327g                |