

Flat Nose Pliers



DESCRIPTION:

Flat nose pliers for professionals with straight, smooth and short jaws

Special pliers made from high grade special steel for extremely high requirements

For gripping, bending and holding

Box joint - double leaf spring

Precise jaw adjustment without backlash

High gloss steel polished surface


Ergonomically formed bicoloured hand guard - dissipative anti-slide material

The pliers have been tested with good results by several test laboratories adequate to DIN EN 61340-5-1, DIN 61340-2-1, DIN 61340-2-3 for work in ESD protected areas

SPECIFICATION:

Length	130 mm
A - Head width	10 mm
B - Head length	22 mm
C - Head thickness	6.5 mm
D - Jaws thickness	1.5 mm
E - Jaws width	3.5 mm
Weight	62 g

Art. Nr.
RND 550-00267



a=10mm/.394"
b=22mm/.866"
c=6.5mm/.250"
d=1.5mm/.059"
e=3.5mm/.138"